



Fluke Ti55FT and Ti50FT FlexCam® Thermal Imagers

Technical Data

The experts' choice for problem solving and preventive/predictive maintenance



Features

	Ti55FT	Ti50FT
High resolution, low noise VOx detector for high quality images	320 x 240	
Temperature range to cover broad industrial applications	-20 °C to +600 °C (-4 °F to 1112 °F)	-20 °C to +350 °C (-4 °F to 662 °F)
High thermal sensitivity for viewing even the smallest temperature differences	≤0.05 °C at 30 °C (50 mK)	≤0.07 °C at 30 °C (70 mK)
180 ° articulating flexible lens to view images in every situation	•	•
Choice of 3 interchangeable lenses to cover every application*	•	•
Large 5 inch high contrast color LCD for a clear picture independent of lighting conditions	•	•
Fully radiometric for detailed temperature analysis and tracking	•	•
SmartFocus for best image quality and accurate temperature measurements	•	•
Windows CE based menu structure for ease of use	•	•
Personalized instrument set-up for multiple person use	•	•
CompactFlash memory cards to store over 1000 IR images plus fully radiometric temperature data	•	•
SmartView® reporting and analysis software included	•	•
AutoCapture for making intermittent problems visible	•	•
On-board analysis functions	•	•
User defined text annotations for simplified reporting	•	•
Built-in visible (visual) light camera	•	•
IR-Fusion blending thermal and visible light images	•	•
IR/Visible Alarm function	•	•
Laser pointer for easy targeting	•	•
Flash and torch light for high quality images in dark environments	•	•

The Fluke Ti55FT and Ti50FT models feature everything needed for virtually any thermography task.

Fluke FlexCam Thermal Imagers come standard with the patent-pending Fluke IR-Fusion® Technology fusing visual (visible light) images with infrared images. SmartView® IR analysis and reporting software is included with each purchase along with free software upgrades for the life of your product.

These models feature 320 x 240 detectors and temperature sensitivity (NETD) down to 0.05 °C (50 mK) in the higher end model.

Choose Fluke FlexCam Thermal Imagers when you need industry leading thermal sensitivity for high resolution, ultra high-quality images.

Typical applications:

- **Troubleshooting**—Pinpointing the location of specific problems in equipment and systems.
- **Preventive/predictive maintenance**—Identify electrical and mechanical problems before they cause failure.
- **Industrial maintenance**—Check whether repairs have been performed correctly.
- **Process monitoring**—Real-time observation to ensure efficient and safe operations.
- **Quality control**—Examine prototypes and refine thermal management designs.
- **Research and development**—Quantify heat patterns to improve product designs.
- **Electronic design**—Circuit board analysis.

*10 mm and 54 mm lenses are optional and are only available at time of initial order.

Detailed specifications

	Fluke Ti55FT	Fluke Ti50FT
Imaging performance		
Field of view (FOV)*	23° horizontal x 17° vertical	
Spatial resolution (IFOV)*	1.30 mrad	
Min focus distance*	0.15 m (5.9 in)	
Thermal sensitivity (NETD)	≤ 0.05 °C at 30 °C (50 mK)	≤ 0.07 °C at 30 °C (70 mK)
Detector data acquisition/image frequency	60 Hz/60 Hz	
Focus	SmartFocus; one finger continuous focus (manual)	
IR digital zoom	2x, 4x, 8x	2x
Detector type	320 x 240 Focal Plane Array, Vanadium Oxide (VOx) Uncooled Microbolometer	
Spectral band	8 μm to 14 μm	
Digital image enhancement	Automatic full time enhanced	
On camera operating modes	Full thermal, full visual light or merged thermal-visual images. Picture-in-Picture	
Visible light camera	1280 x 1024 pixels, full color	
Visible light digital zoom	2x, 4x	2x
Temperature measurement		
Calibrated temperature range	-20 °C to 600 °C (-4 °F to 1112 °F) in three ranges Range one = -20 °C to 100 °C (-4 °F to 212 °F) Range two = -20 °C to 350 °C (32 °F to 662 °F) Range three = 250 °C to 600 °C (482 °F to 1112 °F)	-20 °C to 350 °C (-4 °F to 662 °F) in two ranges Range one = -20 °C to 100 °C (-4 °F to 212 °F) Range two = -20 °C to 350 °C (32 °F to 662 °F)
Accuracy	± 2 °C or 2 % (whichever is greater)	
Measurement modes	Centerpoint, center box (area min/max, average), moveable spots/boxes, user defined field/text annotations, automatic hot and cold point detection, visible color alarm above and below	Centerpoint, center box (area min/max, average)
Emissivity correction	0.1 to 1.0 (0.01 increments)	
Image presentation		
Digital display	13 cm (5 in) diagonal large high-resolution digital display	
LCD backlight	Sunlight readable color LCD	
Video output	RS170 EIA/NTSC or CCIR/PAL composite video	
Palettes	Grayscale, grayscale inverted, blue red, high contrast, hot metal, ironbow, amber, amber inverted	
Optical lenses		
54 mm telephoto lens	High precision Germanium lens Field of view (FOV): 9° horizontal x 6° vertical	
	Spatial resolution (IFOV): 0.47 mrad	
	Min focus distance: 0.6 m (1.97 ft)	
10.5 mm wide angle lens	High precision Germanium lens Field of view (FOV): 42° horizontal x 32° vertical	
	Spatial resolution (IFOV): 2.45 mrad	
	Min focus distance: 0.3 m (0.98 ft)	

*Standard 20 mm Germanium lens

General specifications

	Fluke Ti55FT	Fluke Ti50FT
Image and data storage		
Storage medium	Compact flash card stores over 1000 IR images (1 GB card standard)	
File formats supported	14 bit measurement data included. Exportable Images: bmp, gif, jpg, png, tiff; Data formats: comma separated (csv), tab separated (txt).	
Interface and software		
Interface	Compact flash card reader included	
Software	SmartView; Full analysis and reporting software included	
Laser		
Classification	Class II	
Laser targeting	Laser dot visible on screen when blending thermal and visible image	
Controls and adjustments		
Set-up controls	Date/time, temperature units C/F, language, scale, LCD intensity (high/normal/low)	
Image controls	Level, span, auto adjust (continuous/manual)	
On-screen indicators	Battery status, target emissivity, background temperature and realtime clock	
Power		
Battery type	Li-Ion smart battery, rechargeable, field-replaceable (two included)	
Battery operating time	Two hours continuous operation (per battery)	
Battery charging	Two bay intelligent charger powered via ac outlet	
Continuous ac operation	AC adapter 110/220 V ac, 50/60 Hz	—
Power saving	Automatic shutdown and sleep modes (user specified)	
Environmental and mechanical design		
Operating temperature	-10 °C to +50 °C (14 °F to 122 °F)	
Storage temperature	-40 °C to +70 °C (-40 °F to 158 °F)	
Relative humidity	Operating and storage 10 % to 95 %, non-condensing	
Water and dust resistant	IP54	
Weight (including batteries)	1.95 kg (4.3 lb)	
Camera size (H x W x D)	162 mm x 262 mm x 101 mm (6.5 in x 10.5 in x 4.0 in)	
Other		
Warranty	Two-years	

Ordering information

FLK-Ti50FT-20 IR FlexCam Thermal Imager with IR-Fusion
FLK-Ti55FT-20 IR FlexCam Thermal Imager with IR-Fusion

Included with product

Heavy duty carrying case, 2 rechargeable battery packs, battery charger, ac adapter (with Ti55FT only), video cable, 512 MB compact flash card, compact flash card reader and USB cable, PCMCIA compact flash card reader, neck strap, printed getting started guide, SmartView reporting and analysis, software on CD, complete user manual on CD



Fluke. *Not just infrared.
Infrared you can use.™*

Fluke Corporation
PO Box 9090, Everett, WA U.S.A. 98206

Fluke Europe B.V.
PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:
In the U.S.A. (800) 443-5853 or
Fax (425) 446-5116
In Europe/M-East/Africa +31 (0) 40 2675 200 or
Fax +31 (0) 40 2675 222
In Canada (800)-36-FLUKE or
Fax (905) 890-6866
From other countries +1 (425) 446-5500 or
Fax +1 (425) 446-5116
Web access: <http://www.fluke.com>

©2007-2010 Fluke Corporation.
Specifications subject to change without notice.
Printed in U.S.A. 6/2010 2674273 E D-EN-N