

SpotScan™

Line scanning accessory for spot pyrometers

Fluke Process Instruments is proud to introduce the SpotScan accessory. This accessory is used with Endurance®, Marathon MM, Marathon MR, Modline® 5 and Modline 7 Series sensors. When mounted to the front of the sensor, the accessory allows the user to gather temperature information over a larger area on the target due to the scanning mechanism inside the accessory.

Get more process temperature information!

With SpotScan, you can continue to use the supreme sensor optics to achieve small spot sizes on your target, but with the scanning capability, you can have the spot sweep over the target to see a larger area, providing more data and information for your process. By using the sensor peak picker capabilities, you can see a hot spot over a larger area. Additionally it is important to continuously monitor the analog output for temperature variations that exceed defined limits.


With the SpotScan accessory, you still use the analog temperature output that comes from sensor. By using the various signal conditioning sensor features, you can obtain temperature information over the area you are scanning in a variety of different ways. For instance, if you use the peak picker function, you can look for hot spots over a larger area. Similarly, if you use the averaging or response time function, you can obtain average temperatures over a larger area. In any case, the SpotScan accessory allows you to look at a larger area providing more data to understand your process better.



Sighting Options

The SpotScan accessory provides an innovative way to allow you to sight the instrument or periodically check sighting. Onboard SpotScan accessory controls allow you to manipulate the end or center positions of the scan, as well as the frequency of the scan.

1. If you have a sensor equipped with a laser, you can simply turn the laser on to see exactly where the sensor is aimed.
2. If you have a sensor equipped with only through-the-lens sighting, you can stop the scanning at the end points to make aiming adjustments in this area.



Endurance sensor SpotScan accessory and optional air purge

Standard Features

- Durable housing IP65 enclosure designed to survive in ambient temperatures up to 60 °C (140 °F)
- Air purge option available for use in dusty or dirty environments
- For use with Endurance, Raytek® Marathon MM, Marathon MR, Iacon® Modline 5 and Modline 7 Series sensors
- Sighting achieved with the on board sensor via laser, through-the-lens sighting or video function
- SpotScan controls accessible via removable end-cap
- Externally visible 3-state indicator: stationary, power on, scanning
- Interfaces to SpotScan mounting brackets for tilting and positioning
- Uses sensor DC power supply for easy installation

Highlights

- Easily mounts to the housing of any Endurance, Marathon MM, Marathon MR, Modline 7* or Modline 5 sensor
- Innovative scan mirror positioning capability allows you position mirror at end-points to easily sight and configure mounting of the sensor and accessory

Easy Setup and Installation – Reduce your installation costs

- The SpotScan accessory utilizes the existing sensor DC power supply.
- Optional air purge allows for use in dirty and dusty environments

* Modline 7 requires "7X-XXXX-0-0-2" configuration

General Specifications


Scan Angle	2 – 15° adjustable by control knob		
Scan Frequency	0.5 – 5 Hz adjustable by control knob		
Internal optical path distance	EN1R	31.9 mm	[1.25 in]
	MR	31.9 mm	[1.25 in]
	MM	91.0 mm	[3.58 in]
	Modline 5	99.1 mm	[3.90 in]
	Modline 7	91.0 mm	[3.58 in]
Status Indicator	3-state (stationary, power on, scanning)		
Power Supply	18 – 32 VDC, 12W		
Operating Temperature Range	0 °C – 60 °C (32 °F – 140 °F)		
Storage Temperature	-20 °C – 85 °C (-4 °F – 185 °F)		
Weight	1.98 kg (4.38 lb.)		
Enclosure Rating	IP65 (when sensor is fitted in accessory)		
Standards	CE		

Window	Endurance	Marathon	Modline	Correction Factor
SSA (uses N-BK7 window material)	EN1R	MR1S	5R	0.98 ± 0.02*
	EN1R	MR1S, MM1M	5R, 52, 72	
		MM2M	5G, 7G	0.90 ± 0.05
		MM3M	56,76	
SSB (uses ZnS window material)		MMMT	75	0.75 ± 0.10
		MMG5	77	0.93 ± 0.05
		MMG7	78	0.77 ± 0.10
		MMLT	74	0.73 ± 0.10

* E-Slope correction, depends on measured temperature

Note: SpotScan accessory will interface to only Modline 7 sensors configured as "7X-XXXX-X-X-2"

Dimensions



Applications


To avoid false readings associated with scale buildup on the metal surface, you can use the peak picker function to provide a more accurate temperature measurement of the steel.

While looking at thin wires that are not always in the field-of-view, the SpotScan accessory will allow you to look over a larger area and still see the wires.

Use the SpotScan accessory for web or conveyor hot spot or cold spot monitoring. Mount the sensor and accessory to allow for complete coverage of the area you want to monitor.

With the two SpotScan models available, you can scan high and low temperature applications.

User Interface



Options

Power cables

PSCB7HT	High-temp (180 °C/356 °F) 7.5 m power supply cable includes connector to the accessory
---------	--

Accessories for SpotScan only

SSUAA	SpotScan universal adapter accessory
SSRAM	Right angle mount to attach to SSUAA, SSA or SSB
SSAP	SpotScan air purge accessory

Applications

- Metals processing
- Molten metal/forging
- Hot rolling mills
- Rod/wire mills
- Heat treating & annealing
- Induction heating
- Induction pipe welding
- Butt welding
- Hot spot detection (conveyors, webs, belts)
- Refuse burning
- Carbon graphite production

The Fluke Process Instruments Guarantee

The SpotScan accessory is supported by a 2 year warranty. With a network of trained representatives and agents in over one hundred (100) countries and offices located in the U.S., Germany and China, we provide local service and support you can rely on time after time.

Fluke Process Instruments

Americas

Everett, WA USA

Tel: +1 800 227 8074 (USA and Canada, only)
+1 425 446 6300

solutions@flukeprocessinstruments.com

EMEA

Berlin, Germany

Tel: +49 30 4 78 00 80

info@flukeprocessinstruments.de

China

Beijing, China

Tel: +8610 6438 4691

info@flukeprocessinstruments.cn

Japan

Tokyo, Japan

Tel: +81 03 6714 3114

info@flukeprocessinstruments.jp

Asia East and South

India Tel: +91 22 6249 5028

Singapore Tel: +65 6799 5578

sales.asia@flukeprocessinstruments.com

Worldwide Service

Fluke Process Instruments offers services, including repair and calibration. For more information, contact your local office.

www.flukeprocessinstruments.com